



PRO® and Burford's® are registered trademarks of BAF Industries.



- **Dissolves Window Tint Glue**
- **Excellent Glass Cleaner at Diluted 6:1**
- **Powerful High Ammonia Base**
- **Leaves No Residue**
- **Will Not Reset Glue Like Solvent**

- **Ready To Use Tint Remover**
- **Removal by Hand Wiping**
- **Leaves Glass and Windshields Crystal Clear**
- **Biodegradable**
- **VOC Compliant**

C-64 Window Tint Glue Remover

FEATURES & BENEFITS

C-64 Window Tint Glue Remover is a, ready to use, quick and easy method of removing glue that remains after you have stripped the tinted film from the window. The application causes the glue to dissolve rapidly and won't allow it to reset itself. Potent soaps with added ammonia supply the powerful action of C-64. It leaves the glass crystal clear and is totally removable by hand. It wipes clean with added anti-static protection. Diluted 6:1 it makes a powerful glass cleaner. C-64 will also cut through heavy smoke residue, dirt, oil and grime. Wipes clean as a prep for re-application.

RECOMMENDED FOR

Removal of excess glue left behind when tinted film has been taken off the windows.

APPLICATION

SHAKE WELL BEFORE USING. Peel and remove the tinted film from the window. Place a towel at the base of the glass to catch any excess product. Using a sprayer, apply a heavy coating of C-64 on the glue portion. Let sit 2-3 minutes to dissolve the glue. As glue is dissolving, scrape remaining glue off with razor blade scraper and simply wipe off excess glue residue from glass with a cloth. Spray a light coating and repeat to get a totally residue free surface. For Glass Cleaner

use, dilute C-64 6:1 with water. Spray on and wipe off immediately with a clean towel.

SPECIAL NOTES

Hydro Accudose systems is recommended for most accurate dilution ratios when used as a full strength glass cleaner. Do not use C-64 on CLEAN tinted windows as the product will dissolve the glue holding the tint. Use C-13 Super Glass Gleam or AGC-18 Aerosol Glass Cleaner if non-ammonia product is preferred.

506/511		Accu-Dose 1GPM	
No Tip	3:1	No Tip	3:1
Gray	5:1	Red	5:1

PACKAGING

GALLON / 4 PER CASE